

TITLE: Instapak Quick® RT To Be Offered As Instant Foam Solution For Most Pelican Protector™ Cases

PRODUCTS AFFECTED: Pelican Protector™ Cases, Models 1300 to 1780



1. Completely unfold an Instapak Quick® RT bag and lay on a flat surface. Press hard on the component "A" oval to break the seal.



2. Alternately "pat" back and forth on the "A" and "B" ovals fifteen to twenty times. As soon as the foam begins to expand place the bag into the empty case.



3. As the foam continues to expand, center the product to be packaged, and hold product in place for 30 seconds.

NOTE: Instapak foam expands rapidly so work quickly.



4A. Activate a second bag. Quickly place on top of the product. Close the case lid and lock for 30 seconds so that the foam expands to form a top cushion.



4B. If the product fills more than 50% of the case you can use the convoluted lid foam in the case lid or a second Instapak. Refer to the chart below for appropriate case lid top packs.

Instapak Quick® RT to be used with Pelican 1300 or larger Cases Only

DO NOT use an Instapak bag more than one size larger than we suggest. Serious injury may result. If there is any doubt about what size to use, use multiple small bags rather than one large one.

Instapak Quick is a registered trademark of Sealed Air Corporation

| Instapak Cat. # | Contents | Fits these Pelican Cases |
|---|---|--------------------------|
| 1400IP (1400-408-000) | (6) #10 packs | #1300, 1400 |
| 1500IP (1500-408-000) | (4) #20 packs (bottom) (2) #10 packs (top) | #1430, 1450, 1500 |
| 1520IP (1520-408-000) | (4) #40 packs (bottom) (2) #20 packs (top) | #1440, 1510, 1520 |
| 1550IP (1550-408-000) | (4) #60 packs (bottom) (2) #40 packs (top) | #1550, 1560 |
| 1600IP (1600-408-000) | (4) #80 packs (bottom) (2) #60 packs (top) | #1600, 1610, 1620 |
| 1630, 1640, 1650, 1660, 1690, 1700, 1720, 1750, 1780, 0340, 0350, 0370 Cases. Please call for assistance. | | |

